


## **SP1 EASE OF USE IMPROVEMENTS 2019**



## **Improved Screen Graphics**

provides enhanced visual feedback during roll loading and splice preparation. Icons display average eye mark pitch with in-registration splicing and web break detection, as well as step-by-step recovery instructions.





## Adjustable Core Sensor can be moved +/- 1.5 inches (40mm), according to web graphics requirements.

**WAVE (Width Adaptive Vacuum Effectiveness) Prep Bar** 

spreads vacuum across the bar, correcting web edge curl and eliminating variable web width adjustments. Available on machines ordered beginning Q2 2019.

inadequate air pressure for consistent splicing.



## **SP1 EASE OF USE IMPROVEMENTS 2019**

